



Suitable to use on compact disks, glass, cameras, computer screens, optical lenses, laboratory instruments, cell phones, microscopes, and televisions.

### Easy to use:

For the best performance, soak cloth in water prior to initial use and allow it dry. This will remove any dust from packaging or manufacturing. For dusting, use dry. For cleaning, dampen with water. Avoid oversaturation. If electing to use a cleaner, avoid detergents with bleach and abrasive materials like silica.

Once dirty, hand wash under warm water with liquid detergent or machine wash on a regular cycle. Avoid washing with linty items like towels.

*Product # MFC1 72 wipes per case*








# MFC<sub>1</sub> Staticide Microfiber Cloth

## Lint-free, chemical-free alternative!

Reduce your budget while cleaning safely. The Staticide Microfiber Cloth's sturdy construction lifts dirt, dust, and oil with or without the use of chemicals.

In one motion, this cloth can eliminate the need for harmful cleaners and disposable wipes. This material naturally attracts dust and can withstand multiple machine washings.

This material is soft enough to be safely used on delicate surfaces without scratching. Its light blue color and embossed border make this attractive and fashionable cloth a lovely accessory for the worktable, desk, briefcase, and handbag.

-  **Size: 9" X 9"**
-  **Reusable; machine washable**
-  **Soft; will not scratch delicate surfaces**
-  **No lint**
-  **Non-toxic**
-  **Attractive border**
-  **Light blue**



**ACL Staticide**

840 W. 49th Place · Chicago, IL 60609  
800.782.8420 · 847.981.9212 · fax 847.981.9278  
info@staticide.com · www.aclstaticide.com



ACL Inc. registered to  
ISO-9001 : 2008  
Certificate NO. A10002746