



Dispensing Shot Meters

Dispensing Made Clean & Simple

Jensen Global's 300-S and 500-S compact benchtop dispensers allow for reproducible deposits of a wide range of thin or viscous materials such as solder pastes and masks, adhesives, epoxies, RTV's and silicones, cyanoacrylates, paints and inks. They are excellent for use with pre-filled syringes of materials, or when loading empty syringes.

The analog timer of the 300-S and the digital timer of the 500-S enable the production of a controlled deposit amount. Vacuum pull back in both units assists with a cleaner deposit when materials have tendencies to string.



300-S

FEATURES & ACCESSORIES

- Timer .01 to 30 sec
- Vacuum Pull Back
- Power supply 100-240V
- Durable yet lightweight foot pedal
- 5/32" and 1/4" unique tubing adapter fittings
- Needle samples



500-S

FEATURES & ACCESSORIES

- Timer range .007 to 99.99 sec with range selection from hundredths to thousands
- 10 program storage
- Unique sequential program dispensing
- Interrupt dispense mode & 'teach' mode
- Vacuum pull back
- Power supply 100-240V
- Durable, lightweight foot pedal
- 5/32" and 1/4" quality tubing adapter fittings
- Needle samples

Specifications for 300-S & 500-S

Dimensions Wx HxD

4.50 x 6.25 x 7.75"
11.4 x 15.8 x 19.9 cm

Weight

2.4 lbs (1.09 kg) = 300-S
2.1 lbs (.95 kg) = 500-S

Power Supply

Input 100-240VAC
Output 24VDC 1A

Timer Range

00.01 to 30 seconds (300-S)
00.007 to 99.99 seconds (500-S)

Air Input

35-100 psi (2.4-6.9 bar)

Air Output

1-100 psi (0.1-6.9 bar)

Options for 300-S & 500-S



Needle Kit
120NK



Syringe Kit
120NS



Syringe Stand
D816

Adapters

1CCUSA-C
3A-XC
5A-XC
10A-XC
30A-XC

Syringes

3A-50
5A-40
10A-30
30A-20
50A-15

2 EASY
Ways To Order

OPTION 1: Call (800) 538.1578 with your P.O.

OPTION 2: Use your credit card at **shopeis.com**

For a local EIS branch listing go to **www.eis-inc.com**